




# ROUTE 66 (40 UL)



|                    |                |                 |                 |
|--------------------|----------------|-----------------|-----------------|
| <b>DISTANCE:</b>   | <b>45 FEET</b> | <b>VOLUME:</b>  | <b>23.68 mL</b> |
| <b>RATIO:</b>      | <b>4.00:1</b>  | <b>FORWARD:</b> | <b>11 mL</b>    |
| <b>DROP BRUSH:</b> | <b>45 FEET</b> | <b>REVERSE:</b> | <b>12.68 mL</b> |
| <b>TANKS:</b>      | <b>KEGEL</b>   | <b>PUMP:</b>    | <b>40µL</b>     |




### FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 4     | 40   | 14    | 3    | A - Kegel | 0 → 6    | 5,920 |
| 2 | 12L   | 12R  | 2     | 40   | 14    | 3    | A - Kegel | 6 → 10   | 1,360 |
| 3 | 13L   | 13R  | 3     | 40   | 14    | 3    | A - Kegel | 10 → 16  | 1,800 |
| 4 | 14L   | 14R  | 2     | 40   | 18    | 3    | A - Kegel | 16 → 21  | 1,040 |
| 5 | 15L   | 15R  | 2     | 40   | 18    | 3    | A - Kegel | 21 → 26  | 880   |
| 6 | 2L    | 2R   | 0     | 40   | 18    | 3    | A - Kegel | 26 → 33  | 0     |
| 7 | 2L    | 2R   | 0     | 40   | 26    | 3    | A - Kegel | 33 → 40  | 0     |
| 8 | 2L    | 2R   | 0     | 40   | 30    | 3    | A - Kegel | 40 → 45  | 0     |

### REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 0     | 40   | 30    | 3    | A - Kegel | 45 → 38  | 0     |
| 2 | 14L   | 14R  | 2     | 40   | 18    | 3    | A - Kegel | 38 → 33  | 1,040 |
| 3 | 13L   | 13R  | 2     | 40   | 18    | 3    | A - Kegel | 33 → 28  | 1,200 |
| 4 | 12L   | 12R  | 3     | 40   | 18    | 3    | A - Kegel | 28 → 20  | 2,040 |
| 5 | 11L   | 11R  | 3     | 40   | 14    | 3    | A - Kegel | 20 → 14  | 2,280 |
| 6 | 10L   | 10R  | 2     | 40   | 14    | 3    | A - Kegel | 14 → 11  | 1,680 |
| 7 | 2L    | 2R   | 3     | 40   | 10    | 3    | A - Kegel | 11 → 6   | 4,440 |
| 8 | 2L    | 2R   | 0     | 40   | 10    | 3    | A - Kegel | 6 → 0    | 0     |



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET



SCAN QR CODE TO  
SHARE AND  
DOWNLOAD  
THIS PATTERN

